

Technical data sheet WT108

Specification TEAMBOARD F M700, felt board w.storage compartment

Dimensions in mm

Packaging data

Seat: H: 1075 W: 700 D: 135 Total: H: 1975 W (no ArmR): 700 D: 630 33,6 Weight: kg Volume: т³



Basic equipment		Benefit
General	MDF board with birch Multiplex edge, width: 700 mm. Surface, direct melamine coating, plastic laminate in white. Total thickness: 19 mm. Both sides covered with black felt, suitable for hook-and-loop fastenings. With storage compartment for FLYCHARTS.	The TEAMBOARD provides space for attaching and storing FLYCHARTS and therefore offers an interchangeable whiteboard surface.
Colour finish	Steel parts, powder-coated, black or white.	Consistent appearance even in intensive use.
Base	Natural wooden feet made from ash, untreated.	Optimum stability. Attractive look.
Castors	Soft universal castors with locking function, electrogalvanised.	Mobility and stability.
Materials	All materials are unmixed and recyclable.	Environmentally friendly.
Certification	Quality Management System DIN EN ISO 9001:2015, Regulation (EC) no. 1221/2009 (EMAS), Environmental Management System DIN EN ISO 14001:2015, Occupational Health and Safety Management System DIN EN ISO 45001:2018, Energy Management System DIN EN ISO 50001:2018, EcoVadis Gold, Commitment to sustainability.	High-quality product.
Warranty	10-year warranty according to our current warranty conditions.	Quality guaranteed to last for entire product life.

Disassembly instructions are available upon request for any interstuhl product



Technical data sheet WT108

Specification TEAMBOARD F M700, felt board w.storage compartment

Dimensions in mm

Packaging data

Seat:	H:	1075
	W:	700
	D:	135
Total:	H: W (no ArmR):	1975 700
	D:	630
Weight:	kg	33,6
Volume:	m³	



Options		Benefit
FLYCHARTS	FLYCHART, light whiteboard panel, magnetic, can be written on. Equipped with hook-and-loop backing.	Portable whiteboard for attachment on all felt boards.
Functional hook	Functional steel hook in black or white.	For hanging up jackets, flip charts etc.

Disassembly instructions are available upon request for any interstuhl product